



6167331606

**Soc. out. out earthing contact, enhncd contact prot., B.3/B.7, ant., matt**

**Technical properties**

**Architecture**

Number of poles 2pole

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Mirror depth 8 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line anthracite

Surface appearance matt

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales with enhanced touch protection

**Safety**

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection Enhanced contact protection

With enhanced contact protection Yes

**Identification**

---

Main design line

Berker S.1/B.3/B.7

---

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7