



633023

Rocker switch 3 x 1-pole Off, Module inserts

Technical properties

Architecture

Type of control unit	single rocker
----------------------	---------------

Configuration

Switch mode	3 x 1- pole Off
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	400 V
Frequency	50/60 Hz

Electric current

Switching current	16 AX (200 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	42 mm
Height	71 mm
Width	71 mm

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

