



6765092003

Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,R.1.3,green

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 217,217,217

Design lines special colours green

Material for printing ABS green

Surface appearance glossy

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

Equipment

Type of configuration Laserdruck

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

Safety

REACH conform Yes

RoHS conform Yes

Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
Instructions	
Information text	Insert colour-coded.