



6765096084

**Socket outlet with earthing pin and control LED, Q.x alu velvety, lacquered**

**Technical properties**

**Architecture**

|                 |                |
|-----------------|----------------|
| Fixing mode     | flush-mounting |
| Number of poles | 2pole + earth  |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

**Dimensions**

|                 |       |
|-----------------|-------|
| Insertion depth | 32 mm |
|-----------------|-------|

**Cover, door**

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

**Materials**

|                        |                            |
|------------------------|----------------------------|
| Colour                 | aluminium                  |
| Colour                 | aluminium optics           |
| RAL colour             | RAL 9006 - White aluminium |
| Material / workmanship | lacquered                  |
| Material               | thermoplastic              |
| Surface appearance     | velvety                    |

**Installation, mounting**

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

**Connection**

|                      |                              |
|----------------------|------------------------------|
| Connection terminals | according to IEC 60884-1     |
| Type of connection   | with screw-in lift terminals |

**Use**

|  |                                |
|--|--------------------------------|
| Differentiation characteristic 2 - Sales | with enhanced touch protection |
| Differentiation characteristic 3 - Sales | Screw-in lift terminals        |

**Safety**

|   |    |
|---|----|
| IK protection code against mechanical impacts | 02 |
|---|----|

|                                  |  |
|----------------------------------|--|
| Protection                       | Enhanced contact protection                    |
| With enhanced contact protection | Yes  |
| <b>Identification</b>            |  |
| Main design line                 | Berker Q.1/Q.3/Q.7/Q.9                         |
| Secondary design line(s)         | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |