



6765757004

**Soc.out. earth. pin, enhncd contact prot.,screw-in lift term.,K.5,steel m.finish**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Dimensions

Insertion depth	32 mm
Mirror depth	14.7 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	Stainless steel
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	metal, matt finish
Material	stainless steel
Surface appearance	matt

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

##### Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals

##### Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Berker K.5