



67657901

**Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,1930/glass,bl.gl.**

### Technical properties

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 16 A

#### Dimensions

Insertion depth 31.3 mm

Installation depth, flush-mounted boxes 31 mm

Mirror depth 14.5 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line black

Colour black

Surface appearance glossy

Metallic colour No

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

#### Use

Differentiation characteristic 1 - Sales Installation position variable in 45° steps

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

#### Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

Main design line	Serie 1930/Glas
Secondary design line(s)	Serie 1930 ; Serie 1930 Porzellan Made by Rosenthal ; Serie Glass ; Series R.classic