



6765792045

**Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,R.classic, bl.gl.**

### Technical properties

#### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Dimensions

Insertion depth	31.4 mm
-----------------	---------

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

#### Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

#### Equipment

Type of configuration	Laserdruck
-----------------------	------------

**Use**

---

Differentiation characteristic 1 - Sales	Installation position variable in 45° steps
Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals

---

**Safety**

---

Protection	Enhanced contact protection
With enhanced contact protection	Yes

---

**Identification**

---

Main design line	Serie R.classic
------------------	-----------------

---