



6765792045

Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,R.classic, bl.gl.

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 31.4 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 217,217,217

Colour of design line black

Colour black

Material for printing PC-PMA black

Surface appearance glossy

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

Settings

Shading parameter R1_czarny

Laser parameter R1_schwarz

Equipment

Type of configuration Laserdruck

Use

Differentiation characteristic 1 - Sales Installation position variable in 45° steps

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Protection	Enhanced contact protection
------------	-----------------------------

With enhanced contact protection	Yes
----------------------------------	-----

Identification

Main design line	Serie R.classic
------------------	-----------------