



6768757009

**Soc. out. earthing pin, enhanced contact prot., K.1, p. white glossy**

**Technical properties**

**Architecture**

Fixing mode	flush-mounting
Number of poles	2pole + earth

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Dimensions**

Insertion depth	31.8 mm
Mirror depth	14.7 mm

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes

RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Berker K.1