



6768766012

**Soc. out. earthing pin, enhncd contact prot., Q.x, red velvety**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm
Mirror depth	14.5 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Design lines special colours	red
Colour	red
Colour	red
RAL colour	RAL 3003 - Ruby red
Material	duroplastic
Surface appearance	velvety
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with plug-in terminals

##### Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

##### Safety

IK protection code against mechanical impacts 02

---

Protection Enhanced contact protection

---

With enhanced contact protection Yes

**Identification**

---

Main design line Berker Q.1/Q.3/Q.7/Q.9

---

Secondary design line(s) Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9