



67687901

Soc. out. earthing pin, enhncd contact prot., 1930/glass, black glossy

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 16 A

Dimensions

Insertion depth 31.3 mm

Installation depth, flush-mounted boxes 31 mm

Mirror depth 14.5 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line black

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales Installation position variable in 45° steps

Differentiation characteristic 2 - Sales with enhanced touch protection

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Serie 1930/Glas
Secondary design line(s)	Serie 1930 ; Serie 1930 Porzellan Made by Rosenthal ; Serie Glass ; Series R.classic