



75161093



IP20

B.IQ push-button 1gang, KNX - B.IQ, stainless steel, metal brushed

Technical properties

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 1

Dimensions

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line Stainless steel

Material / workmanship metal brushed

Surface appearance matt

LED control

LED with blue operation LED and 2 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included No

Accessories included

Box for installation in single standard wall boxes

for stainless steel frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

Equipment

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

Safety

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ ; KNX