



75161094

IP20

**B.IQ push-button 1gang, KNX - B.IQ, al., al. anodised**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Functions**

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

**Compatibility**

Extension unit extension unit for light scene push-button

**Controls and indicators**

With LED indication Yes

Number of buttons 1

**Dimensions**

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

**Measurement**

Value transmitter dimming / position value transmitter 1 byte

**Screen**

With display No

**Materials**

Colour of design line Aluminium

Colour aluminium

RAL colour RAL 9006 - White aluminium

Material / workmanship aluminium, anodised

Material Aluminium

Surface appearance matt

Type of surface treatment Anodised

**LED control**

LED with blue operation LED and 2 white status LEDs (labelling field illumination)

**Connection**

Bus coupling unit for bus coupling unit flush-mounted

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Accessories included**

Box	for installation in single standard wall boxes
Matching products	for aluminium frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

**Equipment**

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

**Safety**

Protection index IP	IP20
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ, KNX