



75162091

IP20

Technical properties

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	2

Dimensions

Depth	16.7 mm
Height	88.5 mm
Width	88.5 mm

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	glass polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy
Material family	Glass

LED control

LED	with blue operation LED and 4 white status LEDs (labelling field illumination)
-----	--

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
-----	--

Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ