



75162091

**IP20**

## Technical properties

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

### Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	2
-------------------	---

### Dimensions

Depth	16.7 mm
-------	---------

Height	88.5 mm
--------	---------

Width	88.5 mm
-------	---------

### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

### Screen

With display	No
--------------	----

### Materials

Colour of design line	glass polar white
-----------------------	-------------------

Colour	polarwhite
--------	------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	glass
----------	-------

Type of surface treatment	Painted
---------------------------	---------

Material family	Glass
-----------------	-------

### LED control

LED	with blue operation LED and 4 white status LEDs (labelling field illumination)
-----	--

### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

### Scope of delivery

Bus connection included	No
-------------------------	----

<b>Accessories included</b>	
Box	for installation in single standard wall boxes
<b>Equipment</b>	
Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ
<b>Safety</b>	
Protection index IP	IP20
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
<b>Identification</b>	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ