



75162091

IP20

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 2

Dimensions

Depth 16.7 mm

Height 88.5 mm

Width 88.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line glass polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material glass

Type of surface treatment Painted

Material family Glass

LED control

LED with blue operation LED and 4 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included No

Accessories included

Box	for installation in single standard wall boxes
-----	--

Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

Safety

Protection index IP	IP20
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ