



75162092



IP20

## B.IQ push-button 2gang, KNX - B.IQ, glass black

### Technical properties

#### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit extension unit for light scene push-button

#### Controls and indicators

With LED indication Yes

Number of buttons 2

#### Dimensions

Depth 16.65 mm

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

#### Measurement

Value transmitter dimming / position value transmitter 1 byte

#### Screen

With display No

#### Materials

Colour of design line glass black

Colour black

Surface appearance glossy

Material family Glass

#### LED control

LED with blue operation LED and 4 white status LEDs (labelling field illumination)

#### Connection

Bus coupling unit for bus coupling unit flush-mounted

#### Scope of delivery

Bus connection included No

#### Accessories included

Box for installation in single standard wall boxes

for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

---

**Equipment**

---

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

---

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

---

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

**Identification**

---

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ