



75163092

IP20

B.IQ push-button 3gang, KNX - B.IQ, glass black

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Dimensions

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line glass black

Colour black

RAL colour RAL 9005 - Jet black

Material glass

Type of surface treatment Painted

Material family Glass

LED control

LED with blue operation LED and 6 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included

No

Accessories included

Box for installation in single standard wall boxes

Matching products

for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for glass frames in the same "style" for additional applications, see the Design line B.7

Equipment

Number of actuation points 6

With anti-theft/dismantling protection Yes

Product type: product type: B.IQ

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker B.IQ

Secondary design line(s) Berker B.IQ, KNX