



75164591

Technical properties

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation second operating level via object or 3-button handle ; lockable via 3-button actuation ; one push-button operation for switching, pushing, shutters and dimming

Dimensions

Height 118.1 mm

Width 88.5 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of design line glass polar white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

LED control

LED with blue operation LED and 8 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Supported configuration modes system, PB

Parameterisation single and two push-button operation parameterisable

Scope of delivery

Bus connection included

No

Accessories included

Box for installation in single standard wall boxes

Matching products

for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for glass frames in the same "style" for additional applications, see the Design line B.7

Equipment

Number of actuation points 8

With anti-theft/dismantling protection Yes

Product type: product type: B.IQ

Safety

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker B.IQ

Secondary design line(s) KNX ; Berker B.IQ