



75164591

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation second operating level via object or 3-button handle, lockable via 3-button actuation, one push-button operation for switching, pushing, shutters and dimming

Dimensions

Height 118.1 mm

Width 88.5 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of design line glass polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material glass

Type of surface treatment Painted

LED control

LED with blue operation LED and 8 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Supported configuration modes	system, PB
Parameterisation	single and two push-button operation parameterisable
Scope of delivery	
Bus connection included	No
Accessories included	
Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for glass frames in the same "style" for additional applications, see the Design line B.7
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ