



85655285



IP20

KNX radio wall-transmitter 1gang flat quicklink, S.1/B.3/B.7, ant., matt

Technical properties

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Assembling height	14 mm
-------------------	-------

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Battery

Battery service life [years]	≈ 5
------------------------------	-----

Materials

Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material	thermoplastic
Surface appearance	matt

Equipment

Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

Safety

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	KNX radio- operating systems
--------------------	------------------------------

