



AKA181250ELN



floortrack AKA181250ELN

Technical properties

Configuration

Antibacterial treatment	No
Self-adhesive	No

Dimensions

Trunking height	18 mm
Length	2000 mm
Standard length	2000 mm
Trunking width	125 mm
Width of installed product	125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	8
--	---

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Equipment

Number of fix dividers	1
Compartment quantity	2
Number of channels	2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes