



ATA122008014

**Trunking 12x20,L=2,1m,brown**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 13 mm

Length 2100 mm

Trunking width 24 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 1

Maximum number of cables (Ø 11 mm, 50% fill) 1

**Cover, door**

Lid shape premounted

**Materials**

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 18

Internal/useful cross section 240 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 13

**Equipment**

Cable retainers per meter 2

**Standards**

Approvals EN50085-2-1

European directive RoHs voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

---

Operating temperature

-5...65 °C