



ATA122008014

Trunking 12x20,L=2,1m,brown

Technical properties

Architecture

Fixing mode bottom punched

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 13 mm

Length 2100 mm

Trunking width 24 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 1

Maximum number of cables (Ø 11 mm, 50% fill) 1

Cover, door

Lid shape premounted

Materials

Colour brown

RAL colour RAL 8014 - Sepia brown

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Number of wires 1,5 mm² - 40% filling degree 18

Internal/useful cross section 240 mm²

Number of wires 2,5 mm² - 40% filling degree 13

Equipment

Cable retainers per meter 2

Standards

Approvals EN50085-2-1

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature	-5...65 °C
-----------------------	------------
