



ATA122009010



## Trunking 12x20,L=2,1m,pure white

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	13 mm
-----------------	-------

Length	2100 mm
--------	---------

Trunking width	24 mm
----------------	-------

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
--	---

Maximum number of cables (Ø 11 mm, 50% fill)	1
--	---

#### Cover, door

Lid shape	premounted
-----------	------------

#### Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Transparent	No
-------------	----

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Cable

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	18
--	----

Internal/useful cross section	240 mm <sup>2</sup>
-------------------------------	---------------------

Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	13
--	----

#### Equipment

Number of fix dividers	0
------------------------	---

Number of plugable separators	0
-------------------------------	---

Compartment quantity	1
----------------------	---

Cable retainers per meter	2
---------------------------	---

#### Standards

---

European directive RoHS

voluntary compliance

**Safety**

---

REACH conform

Yes

---

RoHS conform

Yes

---

Halogen free

No

---

Impact strength

IK07

**Use conditions**

---

Operating temperature

-5...65 °C