



ATA122018014

Trunking 12x20,L=2,1m,brown

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 13 mm

Length 2100 mm

Trunking width 24 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 1

Maximum number of cables (Ø 11 mm, 50% fill) 1

Cover, door

Lid shape premounted

Materials

Colour brown

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Number of wires 1,5 mm² - 40% filling degree 14

Internal/useful cross section 240 mm²

Number of wires 2,5 mm² - 40% filling degree 10

Equipment

Number of fix dividers 1

Cable retainers per meter 4

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature

-5...65 °C