



ATA122038014

External corner for ATEHA trunking 12x20 in brown

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Compatibility

Product compatibility LFW

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 12 mm

Length 26.5 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

Colour brown

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 140 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

