



ATA122048014

### Internal corner for ATEHA trunking 12x20mm in brown

#### Technical properties

##### Architecture

Fixing mode Clipped

##### Configuration

Antibacterial treatment No

##### Connectivity

Trunking coupling without coupler

##### Dimensions

Trunking height 12 mm

Length 48 mm

Trunking width 20 mm

##### Cover, door

Lid with softlip No

##### Materials

Material group plastic

Type of surface treatment untreated

##### Installation, mounting

Base punching Without base punching

##### Settings

Angle range 83 / 140 °

##### Accessories included

Accessory configuration Moulded

##### Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

##### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

##### Use conditions

Operating temperature -5...60 °C

