



ATA122048014

### Internal corner for ATEHA trunking 12x20mm in brown

#### Technical properties

##### Architecture

Fixing mode Clipped

##### Configuration

Antibacterial treatment No

##### Connectivity

Trunking coupling without coupler

##### Dimensions

Trunking height 12 mm

Length 48 mm

Trunking width 20 mm

##### Cover, door

Lid with softlip No

##### Materials

Colour brown

RAL colour RAL 8014 - Sepia brown

Material ABS

Material group plastic

Type of surface treatment untreated

##### Installation, mounting

Base punching Without base punching

##### Settings

Angle range 83 / 140 °

##### Accessories included

Accessory configuration Moulded

##### Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

##### Safety

Protection index IP IP40

Impact strength IK07

##### Use conditions

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...60 °C