




ATA122049010



Internal corner for ATEHA trunking 12x20mm in pure white

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 13 mm

Length 48 mm

Trunking width 24 mm

Cover, door

Lid with softlip No

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 140 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C