



ATA122058014

Flat corner for ATHEA trunking 12x20mm in brown

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Dimensions

Trunking height 12 mm

Length 50 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

Colour brown

RAL colour RAL 8014 - Sepia brown

Material ABS

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

Safety

Protection index IP IP40

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C