



ATA122058014

**Flat corner for ATHEA trunking 12x20mm in brown**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Dimensions**

Trunking height	12 mm
Length	50 mm
Trunking width	20 mm

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	ABS
Type of surface treatment	untreated

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	90 °
-------------	------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Safety**

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

Ambient temperature	-5...60 °C
---------------------	------------