



Flat corner for ATHEA trunking 12x20mm in brown

Technical properties

Architecture	
Fixing mode	Clipped
Configuration	
Antibacterial treatment	No
Dimensions	
Trunking height	12 mm
Length	50 mm
Trunking width	20 mm
Cover, door	
Lid with softlip	No
Materials	
Type of surface treatment	untreated
Installation, mounting	
Base punching	Without base punching
Settings	
Angle range	90 °
Accessories included	
Accessory configuration	Moulded
Standards	
Approvals	EN50085-2-1
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
Use conditions	
Operating temperature	-560 °C
temperatur	
Ambient temperature	-560 °C