



ATA122088014

## T piece for ATHEA trunking 12x20mm in brown

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Dimensions

Trunking height 12 mm

Length 20 mm

Trunking width 20 mm

Width 12 mm

#### Cover, door

Lid with softlip No

#### Materials

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Accessories included

Accessory configuration Moulded

#### Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...60 °C