



ATA123038014

**External corner for ATHEA trunking 12x30mm in brown**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	12 mm
Length	26.5 mm
Trunking width	30 mm

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	ABS
Material group	plastic
Type of surface treatment	untreated

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	83 / 140 °
-------------	------------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-5...60 °C
<b>temperatur</b>	
Ambient temperature	-5...60 °C