


ATA123039010



**External corner for ATHEA trunking 12x30mm in pure white**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Dimensions**

Trunking height	13 mm
Length	26.5 mm
Trunking width	32 mm

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

RAL colour	RAL 9010 - Pure white
Material group	plastic
Type of surface treatment	untreated

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	83 / 140 °
-------------	------------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Impact strength	IK07
-----------------	------

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

Ambient temperature	-5...60 °C
---------------------	------------