



ATA123048014

## Internal corner for ATHEA trunking 12x30mm in brown

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 12 mm

Length 48 mm

Trunking width 30 mm

#### Cover, door

Lid with softlip No

#### Materials

Colour brown

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 83 / 140 °

#### Accessories included

Accessory configuration Moulded

#### Standards

European directive RoHS voluntary compliance

#### Safety

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...60 °C