



ATA125009010



Trunking 12x50,L=2,0m,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	13 mm
Length	2000 mm
Trunking width	52 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	3
Maximum number of cables (Ø 11 mm, 50% fill)	3

Cover, door

Lid shape	premounted
-----------	------------

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	44
Internal/useful cross section	550 mm ²
Number of wires 2,5 mm ² - 40% filling degree	36

Equipment

Number of fix dividers	0
Number of plugable separators	0
Compartment quantity	1
Cable retainers per meter	2

Standards

European directive RoHs

voluntary compliance

Safety

Protection index IP

IP40

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Impact strength

IK07

Use conditions

Operating temperature

-5...65 °C