



ATA125028014

**Trunking 12x50,L=2,0m,brown**

**Technical properties**

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill)	3
Maximum number of cables (Ø 11 mm, 50% fill)	3

**Materials**

Type of surface treatment	untreated
---------------------------	-----------

**Cable**

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	37
Internal/useful cross section	550 mm <sup>2</sup>
Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	28

**Equipment**

Compartment quantity	3
Cable retainers per meter	2