



ATA125058014

Flat corner for ATHEA trunking 12x50mm in brown

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	12 mm
Length	78 mm
Trunking width	50 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	ABS
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------