



ATA125059010



Flat corner for ATHEA trunking 12x50mm in pure white

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Dimensions

Trunking height 13 mm

Length 78 mm

Trunking width 52 mm

Cover, door

Lid with softlip No

Materials

RAL colour RAL 9010 - Pure white

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C