



ATA125089010



## T piece for ATHEA trunking 12x50mm in pure white

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Dimensions

Trunking height	13 mm
Trunking width	52 mm
Width	12 mm

#### Cover, door

Lid with softlip	No
------------------	----

#### Materials

RAL colour	RAL 9010 - Pure white
Material	ABS
Material group	plastic
Type of surface treatment	untreated

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

#### temperatur

Ambient temperature	-5...60 °C
---------------------	------------