



ATA163018014

Trunking 16x30,L=2,1m,brown

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 16 mm

Length 2100 mm

Trunking width 32 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 2

Maximum number of cables (Ø 11 mm, 50% fill) 2

Cover, door

Lid shape premounted

Materials

Colour brown

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Number of wires 1,5 mm² - 40% filling degree 28

Internal/useful cross section 420 mm²

Number of wires 2,5 mm² - 40% filling degree 22

Equipment

Number of fix dividers 1

Cable retainers per meter 2

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature

-5...65 °C