



ATA163019010



Trunking 16x30,L=2,1m,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	16 mm
Length	2100 mm
Trunking width	32 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	2
Maximum number of cables (Ø 11 mm, 50% fill)	2

Cover, door

Lid shape	premounted
-----------	------------

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	28
Internal/useful cross section	420 mm ²
Number of wires 2,5 mm ² - 40% filling degree	22

Equipment

Number of fix dividers	1
Number of plugable separators	0
Compartment quantity	2
Cable retainers per meter	2

Standards	
European directive RoHs	voluntary compliance
Safety	
Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...65 °C