



ATA163049010



## Internal corner for ATHEA trunking 16x30mm in pure white

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 16 mm

Length 49.5 mm

Trunking width 32 mm

#### Cover, door

Lid with softlip No

#### Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 83 / 140 °

#### Accessories included

Accessory configuration Moulded

#### Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

#### Use conditions

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...60 °C