



ATA205008014

Trunking 20x50,L=2,0m,brown

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 20 mm

Length 2000 mm

Trunking width 52 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 5

Maximum number of cables (Ø 11 mm, 50% fill) 5

Cover, door

Lid shape premounted

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Number of wires 1,5 mm² - 40% filling degree 69

Internal/useful cross section 900 mm²

Number of wires 2,5 mm² - 40% filling degree 51

Equipment

Cable retainers per meter 2

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature

-5...65 °C