



ATA205019010



Trunking 20x50,L=2,0m,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	20 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	52 mm
----------------	-------

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	5
--	---

Maximum number of cables (Ø 11 mm, 50% fill)	5
--	---

Cover, door

Lid shape	premounted
-----------	------------

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Transparent	No
-------------	----

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	65
--	----

Internal/useful cross section	900 mm ²
-------------------------------	---------------------

Number of wires 2,5 mm ² - 40% filling degree	48
--	----

Equipment

Number of fix dividers	1
------------------------	---

Number of plugable separators	0
-------------------------------	---

Compartment quantity	2
----------------------	---

Cable retainers per meter	2
---------------------------	---

Standards

European directive RoHS

voluntary compliance

Safety

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Impact strength

IK07

Use conditions

Operating temperature

-5...65 °C