



ATA205028014

**Trunking 20x50,L=2,0m,brown**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 20 mm

Length 2000 mm

Trunking width 52 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 4

Maximum number of cables (Ø 11 mm, 50% fill) 4

**Cover, door**

Lid shape premounted

**Materials**

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 61

Internal/useful cross section 900 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 45

**Equipment**

Number of fix dividers 2

Cable retainers per meter 2

**Standards**

Approvals EN50085-2-1

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-5...65 °C