



ATA205068014

## End cap for ATHEA trunking 20x50mm in brown

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 20 mm

Trunking width 50 mm

#### Materials

Material group plastic

Type of surface treatment untreated

#### Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...60 °C