



ATA205088014

T piece for ATHEA trunking 20x50mm in brown

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Dimensions

Trunking height 20 mm

Trunking width 50 mm

Width 20 mm

Cover, door

Lid with softlip No

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C